


normann copenhagen

An Indispensable Companion

Normann Copenhagen launches Porta Table Lamp. As implied by its name, Porta is the first portable lamp in the lighting collection. Characterized by its rounded, organic design cues, the cylinder base and elongated dome shape of the lamp shade contribute to an aesthetic cohesiveness.

The distinctive lamp shade is designed to accommodate the need for pleasant, atmospheric lighting in smaller settings. When turned at a 90-degree angle, the lamp shade takes up less space, allowing it to easily fit into compact spaces such as windowsills, small café tables, or shelves.



normann copenhagen

Collection Overview




Porta Table LampBlack
H 23,5 x W 20,2 x D 11,2 x Ø 6,5 cm



Porta Table LampWhite
H 23,5 x W 20,2 x D 11,2 x Ø 6,5 cm



Porta Table Lamp Grey H 23,5 x W 20,2 x D 11,2 x Ø 6,5 cm



Product facts

Description

Porta Table Lamp consists of a lamp shade resting on a sturdy, rounded base, both of which are made from ABS plastic. A white, acrylic diffuser ensures a pleasant and even glow. A silicone base ring allows the lamp to stand securely. Porta comes with a permanently integrated, rechargable, low-energy LED light source which has 3 light intensity levels: 100%, 70% and 40% and a battery life of 8 hours, 24 hours and 90 hours, respectively. The lamp comes with a USB charging cable with a length of 1 meter.

Designer / Year Of Design

Simon Legald / 2021

Material

ABS plastic and acrylic. **>**

normann

COPENHAGEN

Construction


Porta Table Lamp consists of a lamp shade and base made from ABS plastic and an acryclic diffuser. Beneath the base, a small compartment allows for easily accessible charging, and a discreet tunnel for the charging cable ensures that the lamp can charge while in use. A silicone base ring allows the lamp to stand securely. Porta comes with a permanently integrated, rechargable, low-energy LED light source which has 3 light intensity levels: 100%, 70% and 40% and a battery life of 8 hours, 24 hours and 90 hours, respectively. The lamp comes with a USB charging cable with a length of 1 meter.

Maintenance


Before cleaning, disconnect the power and allow the lamp to cool down for 10 minutes. Mind to clean the surfaces of the lamp only. Clean the lamp with a soft, dry cloth only. If necessary, wipe the surface of the lamp with a soft, damp sponge or cloth, and wipe immediately with a dry cloth. Do not use alcohol or other solvents to clean the product and avoid using abrasive or rough sponges.

Test

CE-EMC test with reference to EN55015, EN61547
CE-RoHS Verification with reference to 2011/65/EU
and its amendment 2015/863/EU
211 SVHCs under REACH Directive
Safety test for lithium battery IEC62133
FCC sDoC with reference to Part 15
DOE and CEC
California Prop 65 (Test for total lead and total phthalate)
China RoHS
RCM SDoC



normann



normann

COPENHAGEN

Contact

Normann Copenhagen

Niels Hemmingsens Gade 12, 1153 Copenhagen, Denmark normann@normann-copenhagen.com +45 35 55 44 59



COPENHAGEN